


## Web cleaner adhesive rolls

A 'contact' or 'particle transfer' web cleaner (image shows a Teknek system), typically consists of a blue elastomer roller and an adhesive roller (2 each for a double sided system). The elastomer roller runs in contact with the substrate and picks up dust and debris particles. The elastomer roller rotates and releases the contamination onto the adhesive roller. When the adhesive roller becomes so full that it can no longer pick up debris from the elastomer roller, a sheet is removed to reveal a clean adhesive layer beneath.

Advanced Supplies adhesive rolls are interchangeable with virtually all makes of contact web cleaner and typically contain 17% more material than the competitors.



The Image below shows a double sided web cleaner on a Nilpeter label press.



The adhesive rolls are changed by drawing out the top and/or bottom carriage as shown below

